





1 INSTRUCTIONS AND RECOMMENDATIONS



Switch off the mains before commencing any work




Same connection for a Dual HP mechanism
ref 087-480



For single units, use casings 50mm deep,
diameter 67 or 68mm

2 WIRING




- Connect the 2 cables (black and red) of your installation to the mechanism
- Cable Ø2.5mm² Maximum

3 FITTING

After wiring according to the instructions, place the mechanism in the flush-mount box and screw on the plate according to the diagram opposite.


Screws supplied with the flush-mount box.



4 TABLE OF RELEVANT REFERENCES

Reference and description:

Compatible with:




087-470G S HP WHITE
087-471G S HP BLACK
087-480G D HP WHITE
087-481G D HP BLACK

Confidence and Fascination Collection



087-470B S HP WHITE
087-471B S HP BLACK
087-480B D HP WHITE
087-481B D HP BLACK

Désir, Karo and Hitera Collection



087-470W S HP WHITE
087-471W S HP BLACK
087-480W D HP WHITE
087-481W D HP BLACK

Iris Collection

5 CERTIFICATIONS

